

VWR® cell culture media



Discover the new range of VWR® cell culture media: Basic media, buffer, separation media, water, and supplements. Manufactured in Europe for short delivery time.



MEDIA

- DMEM
- RPMI
- MEM
- Ham's F12
- Drosophila Medium
- McCoy's 5A
- Medium 199



BUFFER

- DPBS
- PBS



SEPARATION MEDIA

- Lymphocyte separation media from whole blood (optimized density 1.077 g/ml)



WATER

- Cell culture water



SUPPLEMENT - REAGENT

- L-Glutamine
- Antibiotic
- Trypsin
- BSA

Description	Pack size	Type	Hepes	L-Glutamine	Phenol Red	Sodium Pyruvate	Stable Glutamine	Calcium	Magnesium	Sodium Bicarbonate	Cat. no
DMEM Low Glucose w/ L-Glutamine w/ Sodium Pyruvate	500 ml	Media	NO	YES	YES	YES	NO	YES	YES	YES	VWRC392-0407
DMEM Low Glucose w/o L-Glutamine w/ Sodium Pyruvate	500 ml	Media	NO	NO	YES	YES	NO	YES	YES	YES	VWRC392-0408
DMEM - F12 w/o L-Glutamine w/o Hepes	500 ml	Media	NO	NO	YES	YES	NO	YES	YES	YES	VWRC392-0409
DMEM - F12 w/o L-Glutamine w/o Hepes w/o Glucose	500 ml	Media	NO	NO	YES	YES	NO	YES	YES	YES	VWRC392-0410
DMEM - F12 w/ stable Glutamine w/ 15 mM Hepes	500 ml	Media	YES	NO	YES	YES	YES	YES	YES	YES	VWRC392-0411
DMEM - F12 w/ L-Glutamine w/ 15 mM Hepes	500 ml	Media	YES	YES	YES	YES	NO	YES	YES	YES	VWRC392-0412
DMEM High Glucose w/o L-Glutamine w/o Sodium Pyruvate	500 ml	Media	NO	NO	YES	NO	NO	YES	YES	YES	VWRC392-0413
DMEM High Glucose w/ L-Glutamine w/o Sodium Pyruvate	500 ml	Media	NO	YES	YES	NO	NO	YES	YES	YES	VWRC392-0414
DMEM High Glucose w/ stable Glutamine w/ Sodium Pyruvate	500 ml	Media	NO	NO	YES	YES	YES	YES	YES	YES	VWRC392-0415
DMEM High Glucose w/ L-Glutamine w/ Sodium Pyruvate	500 ml	Media	NO	YES	YES	YES	NO	YES	YES	YES	VWRC392-0416
DMEM High Glucose w/o L-Glutamine w/ Sodium Pyruvate	500 ml	Media	NO	NO	YES	YES	NO	YES	YES	YES	VWRC392-0417
Ham's F12 w/ L-Glutamine	500 ml	Media	NO	YES	YES	YES	NO	YES	YES	YES	VWRC392-0418
Schneider's Drosophila Medium	500 ml	Media	NO	YES	NO	NO	NO	YES	YES	YES	VWRC392-0419
McCoy's 5A w/ L-Glutamine	500 ml	Media	NO	YES	YES	NO	NO	YES	YES	YES	VWRC392-0420
Medium 199 w/ Hanks' Salts w/ L-Glutamine	500 ml	Media	NO	YES	YES	NO	NO	YES	YES	YES	VWRC392-0421
MEM w/ Earle's Salts w/ L-Glutamine	500 ml	Media	NO	YES	YES	NO	NO	YES	YES	YES	VWRC392-0422
MEM w/ Earle's Salts w/o L-Glutamine w/ NEAA	500 ml	Media	NO	NO	YES	NO	NO	YES	YES	YES	VWRC392-0423
MEM w/ Earle's Salts w/o L-Glutamine	500 ml	Media	NO	NO	YES	NO	NO	YES	YES	YES	VWRC392-0424
RPMI 1640 w/o L-Glutamine w/ 25 mM Hepes	500 ml	Media	YES	NO	YES	NO	NO	YES	YES	YES	VWRC392-0425
RPMI 1640 w/ L-Glutamine w/ 25 mM Hepes	500 ml	Media	YES	YES	YES	NO	NO	YES	YES	YES	VWRC392-0426
RPMI 1640 w/ stable Glutamine	500 ml	Media	YES	NO	YES	NO	YES	YES	YES	YES	VWRC392-0427
RPMI 1640 w/ L-Glutamine	500 ml	Media	NO	YES	YES	NO	NO	YES	YES	YES	VWRC392-0428
RPMI 1640 w/o L-Glutamine	500 ml	Media	NO	NO	YES	NO	NO	YES	YES	YES	VWRC392-0429
RPMI 1640 w/o L-Glutamine w/o Phenol Red	500 ml	Media	NO	NO	NO	NO	NO	YES	YES	YES	VWRC392-0430

Description	Pack size	Type	Sterile	Endotoxin	Pyrogen Free	Calcium	Magnesium	Cat. no
Lymphocyte Separation Media	100 ml	Separation Media	YES	< 10 EU/ml				VWRC392-0431
Lymphocyte Separation Media	500 ml	Separation Media	YES	< 10 EU/ml				VWRC392-0432
Dulbecco's Phosphate Buffered Saline w/o Ca/Mg	1000 ml	Buffer	YES	< 1 EU/ml		NO	NO	VWRC392-0433
Dulbecco's Phosphate Buffered Saline w/o Ca/Mg	500 ml	Buffer	YES	< 1 EU/ml		NO	NO	VWRC392-0434
Dulbecco's Phosphate Buffered Saline 10X w/o Ca/Mg	500 ml	Buffer	YES	< 1 EU/ml		NO	NO	VWRC392-0440
Phosphate Buffered Saline (PBS), pH 7,4	500 ml	Buffer	YES	< 1 EU/ml		NO	NO	VWRC392-0442
Cell Culture Water Pyrogen free	1000 ml	Water	YES	< 0,005 EU/ml	YES			VWRC392-0438
Cell Culture Water Pyrogen free	500 ml	Water	YES	< 0,005 EU/ml	YES			VWRC392-0439
L-Glutamine 100X, 200mM	100 ml	Supplement	YES	< 10 EU/ml				VWRC392-0441
Penicillin-Streptomycin Solution 100X	100 ml	Antibiotic	YES	< 0,1 EU/ml				VWRC392-0406
Trypsin-EDTA 1X in solution w/o Ca/Mg w/ Phenol Red	100 ml	Dissociation Reagent	YES					VWRC392-0435
Trypsin 0.25% - EDTA in HBSS w/o Ca/Mg w/ Phenol Red	100 ml	Dissociation Reagent	YES					VWRC392-0436
Trypsin-EDTA 1X in PBS w/o Ca/Mg w/o Phenol Red	100 ml	Dissociation Reagent	YES					VWRC392-0437
Trypsin-EDTA 10X	100 ml	Dissociation Reagent	YES					VWRC392-0459
Bovine Serum Albumin (BSA) Lyophilised pH -7	100 g	Albumin bovine serum						VWRC392-0443
Bovine Serum Albumin (BSA) Lyophilised pH -7	500 g	Albumin bovine serum						VWRC392-0444
Bovine Serum Albumin (BSA) Lyophilised pH -7	1 Kg	Albumin bovine serum						VWRC392-0445
Bovine Serum Albumin (BSA) Protease Free Lyophilised	100 g	Albumin bovine serum						VWRC392-0446
Bovine Serum Albumin (BSA) Protease Free Lyophilised	500 g	Albumin bovine serum						VWRC392-0447
Bovine Serum Albumin (BSA) Protease Free Lyophilised	1 Kg	Albumin bovine serum						VWRC392-0448
Bovine Serum Albumin (BSA) 30 % liquid	100 ml	Albumin bovine serum	YES					VWRC392-0449
Bovine Serum Albumin (BSA) 30 % liquid	500 ml	Albumin bovine serum	YES					VWRC392-0450
Bovine Serum Albumin (BSA) 30 % liquid	1 L	Albumin bovine serum	YES					VWRC392-0451

Setting science in motion to create a better world



AUSTRIA

VWR International GmbH
Graumanngasse 7
1150 Wien
Tel.: +43 1 97 002 0
info.at@vwr.com

BELGIUM

VWR International bv
Researchpark Haasrode 2020
Geldenaaksebaan 464
3001 Leuven
Tel.: +32 (0) 16 385 011
vwr.be@vwr.com

CZECH REPUBLIC

VWR International s. r. o.
Veetee Business Park
Pražská 442
CZ - 281 67 Stříbrná Skalice
Tel.: +420 321 570 321
info.cz@vwr.com

DENMARK

VWR International A/S
Tobaksvejen 21
2860 Søborg
Tel.: +45 43 86 87 88
info.dk@vwr.com

FINLAND

VWR International Oy
Valimatie 17-19
00380 Helsinki
Tel.: +358 (0) 9 80 45 51
info.fi@vwr.com

FRANCE

VWR International S.A.S.
Immeuble Estréo
1-3 rue d'Aurion
93114 Rosny-sous-Bois cedex
Tel.: 0 825 02 30 30* (national)
Tel.: +33 (0) 1 45 14 85 00
(international)
info.fr@vwr.com
* 0,18 € TTC/min + prix appel

GERMANY

VWR International GmbH
Hilpertstraße 20a
D - 64295 Darmstadt
Tel.: 0800 702 00 07* (national)
Tel.: +49 (0) 6151 3972 0 (international)
info.de@vwr.com
*Freecall

HUNGARY

VWR International Kft.
Simon László u. 4.
4034 Debrecen
Tel.: +36 52 521130
info.hu@vwr.com

IRELAND

VWR International Ltd
Orion Business Campus
Northwest Business Park
Ballycoolin
Dublin 15
Tel.: +353 (0) 1 88 22 222
sales.ie@vwr.com

ITALY

VWR International S.r.l.
Via San Giusto 85
20153 Milano (MI)
Tel.: +39 02 3320311
info.it@vwr.com

THE NETHERLANDS

VWR International B.V.
Postbus 8198
1005 AD Amsterdam
Tel.: +31 (0) 20 4808 400
info.nl@vwr.com

NORWAY

VWR International AS
Brynsalleen 4,
0667 Oslo
Tel.: +47 22 90 00 00
info.no@vwr.com

POLAND

VWR International Sp. z o.o.
Limbowa 5
80-175 Gdansk
Tel.: +48 58 32 38 200
info.pl@vwr.com

PORTUGAL

VWR International - Material de
Laboratório, Lda
Centro Empresarial de Alfragide
Rua da Indústria, nº 6
2610-088 Amadora
Tel.: +351 21 3600 770
info.pt@vwr.com

SPAIN

VWR International Eurolab S.L.U.
C/ Tecnología 5-17
A-7 Llinars Park
08450 - Llinars del Vallès
Barcelona
Tel.: +34 902 222 897
info.es@vwr.com

SWEDEN

VWR International AB
Fagerstagatan 18b
163 94 Stockholm
Tel.: +46 (0) 8 621 34 20
kundservice.se@vwr.com

SWITZERLAND

VWR International GmbH
Lerzenstrasse 16/18
8953 Dietikon
Tel.: +41 (0) 44 745 13 13
info.ch@vwr.com

UK

VWR International Ltd
Customer Service Centre
Hunter Boulevard - Magna Park
Lutterworth
Leicestershire
LE17 4XN
Tel.: +44 (0) 800 22 33 44
uksales@vwr.com

CHINA

VWR (Shanghai) Co., Ltd
Bld.No.1, No.3728 Jinke Rd,
Pudong New District
Shanghai, 201203- China
Tel.: 400 821 8006
info_china@vwr.com

INDIA

VWR Lab Products Private Limited
No.139, BDA Industrial Suburb,
6th Main, Tumkur Road, Peenya Post,
Bangalore, India - 560058
Tel.: +91 80 28078400
vwr_india@vwr.com

KOREA

Avantor Performance Materials Korea
Ltd
2F ACE Gwanggyo Tower I, Daehak
4ro 17
Yeongtong-gu Suwon, Korea 16226
Tel.: +82 31 645 7256
saleskorea@avantorsciences.com

MIDDLE EAST & AFRICA

VWR International FZ-LLC
Office 203, DSP Lab Complex,
Dubai Science Park,
Dubai, United Arab Emirates
Tel.: +971 4 5573271
Info.mea@vwr.com

SINGAPORE

VWR Singapore Pte Ltd
18 Gul Drive
Singapore 629468
Tel.: +65 6505 0760
sales.sg@vwr.com

GO TO [VWR.COM](https://www.vwr.com) FOR THE LATEST NEWS, SPECIAL OFFERS AND DETAILS FROM YOUR LOCAL VWR SUPPORT TEAM